

SK10



Automation Grade	SEMI	Fully	Use Intensity	LOW	Medium	High
Format Setting	MANUAL	Automatic	Box Dimension	Small	MEDIUM	Large

DATASHEET SAFE • SUSTAINABLE • SIMPLE


Semi-Automatic Case Sealer


The **SK10** is a new semi-automatic case sealing machine designed and engineered by SIAT specifically for medium fixed sized boxes. SK10 is the ideal case sealing machine for a variety of industries like food and beverage, chemical, clothing, textiles, electronics and furniture.

KEY FEATURES

- ✓ Practical Seals upper & lower flaps of cardboard cases or cartons
- ✓ Added Protection Lockable electric isolation switch
- ✓ **Safety First** Central emergency stop to work safety on both sides of the machine
- ✓ **Taping Heads** Available with K11 or K12 taping heads
- ✓ Simple Operation Intuitive and quick machine set-up
- ✓ **Quality Build** Best-In-Class components with SIEMENS electrics
- ✓ New feature Top taping head removable
- ✓ Improved Design Quick release Taping Heads (Top & Bottom – No tools required)
- ✓ **CE compliant** Engineered and produced in Italy according to EU safety standards

MACHINE DIMENSIONS





Machine Dimensions			
Min (mm) Max (mm)			
Total H	1.260	1.600	
H Bench	H Bench 485		
W	689	689	
W Bench	572	572	
L	1.080	1.080	

Standard Power Supply			
380/415V - 50Hz - 3ph			
440V - 60Hz - 3ph			
Amps 1,54			
Power kW 0,13			
Phase	3Ph + PE		




DATASHEET

Technical Data		
Belt position	Bottom	
Box Size	Medium	
Min / Max box weight	2 - 30 kg	
Default Taping Head	K11R for 2" = 50 mm	
Alternative Taping Heads	K12R for 3" = 75 mm	
Power Consumption (std.)	0,13 kw	
Air Consumption (NL/Cycle)	-	
Operator Side	Left (std.) / Right	
Tape width (mm)	50 (std.) / 75	
Tape Leg (mm)	70 (std.) / 50 / 30	
Ingress Protection Code	IP54	
Ambient Operating Temperature	5 – 40 °C	
Maximum level of noise	Depending on tape quality	
Features		
Removable Top Taping-Head	•	
Removable Bottom Taping-Head	•	
Adjustable Tape Leg	•	
Pre-Installed & Easy-To-Mount	•	
Adjustable Tape Contact Pressure	•	
Autom. Box Format Setting	-	
Flap Folding Function	-	
Belt Speed Selection	-	
Fully Automatic Operation	-	
SIAT Taping-Logic on board	-	

MORE MACHINE DIMENSIONS

Length x Width		1.080 x 689
Workbench Width		570
Height H	(std. legs)	1.260 - 1.600
Height H1	(std. legs + wheels AS77)	1.370 – 1.710
Height H2	(opt. legs AS80)	1.410 - 1.760
Height H3	(opt. legs AS80 + wheels AS77)	1.520 - 1.870
Workbench Height Z	(std. legs)	485 – 825
Workbench Height Z1	(std. legs + wheels AS77)	595 – 935
Workbench Height Z2	(opt. legs AS80)	645 – 980
Workbench Height Z3	(opt. legs AS80 + wheels AS77)	755 – 1.090














BOX DIMENSIONS & PRODUCTIVITY

*140 mm with 50 mm taping head 170 mm with 75 mm taping head

Box Dimensions	L (mm)	W (mm)	H (mm)
Min.	150	140*	90**
Max.	∞	500	500

** 90 mm high box manageable with 30 mm tape leg 100 mm high box manageable with 50 mm tape leg 120 mm high box manageable with 70 mm tape leg




Max. production capacity: **Up to 1.200* BPH**

*Based on the shortest processible box length and provided an optimum continous box infeed by the operator.

DROCESSABLE TABES

Base Material	PVC / OPP / PET / Paper*
Adhesive Type	Solvent / Hot Melt / Acrylic
Special Tape	Filament-Tape** / Safety-Seal-Tape***

*with limitations **special tape cutting blade required ***need of a test might be necessary



	K11R / K12R
Α	Max. 410 mm
В	50 / 75 mm
С	76 mm


BOX REQUIREMENTS

Quality result of the taped box depends on the general box quality and dimensional accuracy, as well as the quality of tape used.

Box Types: FEFCO 0201 - RSC

[other types may be possible as well]

	Underfilling	Overfilling	Weak Boxes
Adverse Impact Factors			



OPTIONS & ACCESSORIES

- Energy Saving Kit
- End/Break Tape Device
- Operation side "Right" (std. "Left")
- Special cutting blades filament-tape
- Taping Head for 75mm width
- Power Supply 220/230V 50hz 1ph
- Higher Legs
- Casters / Wheels
- Extendable Roller Conveyors
- Fix Roller Conveyors
- Box Holder

MORE DETAILS

Videos and further information can be found on our website or SIAT Youtube channel.





